




what **great systems** are built on.™

A Group brand | **legrand**



Adjustable Rackshelf, 2 RU, 23.5" to 32"D

VDS

The VDS shelf is a partially vented mounting solution for most deep equipment. This shelf has a front to rear mounting adjustment range from 23-1/2" to 32". NOTE: Fits in racks with a minimum 23-1/2" from front to rear rail.

Features

Key Specifications

Resources

Compatible Products

Features

- 2-space, vented shelf for heavy, deep equipment
- Mounting range from 23.5" to 32" (minimum 25.5" overall depth)
- Substantial 200 lb. weight capacity
- Steel construction, with black powder coat finish

Key Specifications

General Info

Finish Type: Black Powder Coat

UL Standards Tested: 1678

Assembly/Installation Information

Mounting Points: 4

Listing Agencies/Third Party Information

RoHS: Yes

Greenguard: Yes

Dimensions

Mounting Depth Max: 32.5

Mounting Depth Min: 23.5

Usable Depth: 25.6"

Capacity Weight (US): 200

Technical Information

UL Load Capacity: 350

Material: Steel

Depth: 26.25"

Height: 3.5"

Width: 19"

Primary Package Weight (US): 15.5

Rack Units: 2

Resources

Instruction Sheet

INST,VDS

PDF (573.8 KB)

Compatible Products

- [Rackshelf Thermal Options](#)



COMP-COOL-3

Component Cooler, 8 CFM, 3 pc.



COMP-COOL50

Component Cooler, 50 CFM



COMP-COOL50P

Component Cooler, 50 CFM, w/Platform



ICOMP-COOL

Component Cooler, 8 CFM, 220V



ICOMP-COOL-3

Component Cooler, 8 CFM, 3 pc., 220V



ICOMP-COOL50

Component Cooler, 50 CFM, 220V



ICOMP-COOL50P

Component Cooler, 50 CFM, w/Platform, 220V

© 2015 Middle Atlantic. All Rights Reserved.