

PART#/PRODUCT SEARCH

1005CK

GO >>

[Item Index](#)

[Mode Catalog](#)
[Lenline Part# Convert](#)
[AC Adapters](#)
[Audio Products](#)
[Battery Holders](#)
[Bottles and Dispensers](#)
[Brushes](#)
[Buzzers/Alarms](#)
[CATV Products](#)
[Circuit Breakers](#)
[Coaxial Connectors](#)
[Computer Accessories](#)
[Connectors](#)
[DC Power Products](#)
[Earphones/Microphones](#)
[Fans](#)
[Fuseholders/Fuses](#)
[Hardware](#)
[IC Sockets](#)
[Knobs](#)
[LED Products](#)
[Lamps/Pilot Lamps](#)
[Miscellaneous Items](#)
[Plastic Boxes](#)
[Potentiometers/L-Pads](#)
[Power Cords/Jacks/Bars](#)
[RF Adapters](#)
[Relays](#)
[Rubber Feet/Grommets](#)
[Speakers/Speaker Wire](#)
[Switches](#)
[Telephone Products](#)
[Test Equipment](#)
[Tools/Tool Cases](#)
[Transformers](#)
[Video Products](#)
[Wiring Products](#)
[Latent Fingerprint Brush](#)



Enlarge

[An explanation of brush design](#)

DOUBLE ENDED SERIES (ANTI-STATIC)

This Series has two sizes with two end styles (tapered and flat) to fit your needs. Fibers are mechanically clamped inot the handle for maximum fiber retention so that no adhesives can leach out and contaminate surface being cleaned. Brushes are available with Horse Hair (HH) or Hog Bristle (CK) material. Handle material for 1005 is Stainless Steel, and the 1010 handle is Zink Plated Steel.

Bristle Material	Hog Bristle
Handle Length	4 1/2"
Diameter	3/16"
Bristle Trim Length	1/4" - Tapered; 1/2" - Flat
Turf Diameter (Oval)	Oval
Use	Short end for haeavy duty scrubbing. Chiseled end to reach and scrub tight corners.

1005CK [Bulk](#)