



SPECIFICATIONS:

Electrical

Rated Power: 0.06W
 Rated Voltage: 150V AC
 Residual Resistance: Terminal 1-2: < 3Ω; Terminal 2-3: <5Ω
 Rotational Noise: Less than 47mV
 Insulation Resistance: 500V DC, >100MΩ
 Withstand Voltage: 1 minute at 800V AC

Mechanical

Total Rotation Angle: 300° ± 5°
 Rotational Life: 10,000 cycles
 Operating Temperature: -20°C - 50°C

Mode Part #	Overall Resistance	Type
62-243-0	5KΩ ± 20%	Linear
62-234-0	10KΩ ± 20%	Log (audio)
62-244-0	10KΩ ± 20%	Linear
62-246-0	50KΩ ± 20%	Linear
62-247-0	100KΩ ± 20%	Linear
62-248-0	500KΩ ± 20%	Linear

TITLE		SCALE
ROTARY POTENTIOMETER		2 : 1
DRAWING NO. 62-2XX(2)		
		UNITS mm
FILE NAME	62-2XX(2).pdf	SHEET 1/1



Mode Electronics Part Number 'multi-parts'