



POSITION	A	B	C	d	D	e	E
09M	16.92	25.00	30.8	03	08.31	04	11.08
15M	25.25	33.30	39.2	06	16.62	07	19.39
25M	38.96	47.10	53.1	11	30.47	12	33.24
37M	55.42	63.50	69.4	17	47.09	18	49.86




NOTE:

Electrical

- Current Rating: 3 Amps
- Contact Resistance: < 15 Milliohms
- Insulation Resistance: > 3000 Megaohms
- Dielectric: 1000V @ 1 Minute
- Operating Temp.: -55°C to 105°C

Materials

- Insulator: PBT Glass Filled UL 94V-0
- Contacts: Brass or Phosphor Bronze
- Shell: Steel
- Contact Plating: Gold Flash
- Shell Plating: Tin over Copper plating



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: ±0.10mm

TITLE		SCALE
MALE RIGHT ANGLE P.C. MOUNT D-SUB		NTS
DRAWING NO.	30-41X	
	UNITS	mm
FILE NAME	30-41X.pdf	SHEET 1/1