



UNC #4-40 Hexscrew

M/F GENDER CHANGER
PIN OUT: 9Male

9Female

1	-----	1
2	-----	2

8	-----	8
9	-----	9
G	-----	G

Label: yellow color with black character
One side: MINI GENDER CHANGER
The other side: U.S.A. PATENT 5199906 GENERAL CHANGER

SPECIFICATION
INSULATOR: PBT Glass fibre reinforced UL 94 VO
CONTACT: Brass
CONTACT PLATING: Gold plated over nickel
SHELL: Tin plated shell
CURRENT RATING: 3 AMP
DIELECTRIC STRENGTH: 1000V AC for one minute
INSULATOR RESISTANCE: 1000MΩ min at 500V DC
TEMPERATURE: -55°C—+105°C

TITLE		SCALE
RS232 GENDER CHANGER		NTS
DRAWING NO.	32-022	
		UNITS mm
FILE NAME	32-022.pdf	SHEET 1/1



Mode Electronics Part Number 32-022-0