




**34-630-0**



**UL**  
E98707

**SP**  
179603



**34-631-0**   **34-634-0**  
**34-632-0**   **34-635-0**  
**34-633-0**   **34-636-0**

**Material: UL approved NYLON 66, 94V-2 (Black)**

Mode Part Number	Cross Section Shape	Wires Accomodate		Mounting Hole		Part Length D	Max. Chassis Thickness F	Packing
		UL	Size	A	B			
34-630-0	Flat	SPT-1 / SPT-2	3 x 5.6 / 3.8 x 7.1	12.7	11.8	17.7	1.8 ~ 2.6	100pcs
34-631-0		SPT-1 # 18	3.0 x 5.6	11.0	9.9	10.3	1.0 ~ 1.6	100pcs (1000pcs)
34-632-0		SPT-1 # 18	3.0 x 5.6	11.0	9.9	10.3	1.9 ~ 2.5	
34-633-0	Round	SVI, SVT 3C # 18	6.2φ ~ 7.4φ	12.7	11.5	11.0	0.5 ~ 1.6	
34-634-0		SVI, SVT 3C # 18	6.2φ ~ 7.4φ	12.7	11.5	11.0	1.8 ~ 2.5	
34-635-0		SJ, SJT, 3C # 16	8.2φ ~ 9.2φ	15.9	14.0	14.8	0.5 ~ 1.6	
34-636-0		SJ, SJT, 3C # 16	8.2φ ~ 9.2φ	15.9	14.0	14.8	1.9 ~ 3.2	

TITLE		SCALE
<b>STRAIN RELIEF BUSHINGS</b>		<b>NTS</b>
DRAWING NO. <b>34-63X</b>		
		UNITS    mm
FILE NAME     34-63X.pdf		SHEET   1/1



**Mode Electronics Part Number 'multi-parts'**