



Specification

- 1. Contact Arrangement: Open, Closed Loop
- 2. Switching Current (Max): 0.25A
- 3. Switching Voltage (Max): 30V DC
- 4. Insulation Resistance: 100 MΩ Min
- 5. Switch Cycle: 5x10 cycle at 30V 0.1A DC
- 6. Temperature: -20 °C to +55 °C
- 7. Case: ABS - 707

TITLE		SCALE
MAGNETIC SWITCH		NTS
DRAWING NO. 47-600		
		UNITS mm
FILE NAME 47-600.pdf		SHEET 1/1