



**SPECIFICATIONS:**

**Materials**

Insulator: PBT-4115, Rated UL94V-0  
 Contacts: Phosphor Bronze  
 Contact Plating: 50 $\mu$ " Nickel (Underplate)  
 Gold Flash (Contact Area)  
 Insulator Color: Black

**Electrical**

Current Rating: 1 Amps Max.  
 Contact Resistance: 15 m $\Omega$  Max.  
 Insulation Resistance: 1000 M $\Omega$  Min. at 500 VDC  
 Dielectric Withstanding: 1000 VAC / Minute  
 Operating Temp.: -55 $^{\circ}$ C to 105 $^{\circ}$ C

TITLE		SCALE
<b>SHORT SHUNT</b>		<b>NTS</b>
DRAWING NO.	<b>36-100</b>	
		UNITS mm
FILE NAME	36-100.pdf	SHEET 1/1



**Mode Electronics Part Number 36-100-0**