


2.54* NO. OF (POSITION-1)±0.1 PER ROW



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: ±0.10mm

SPECIFICATION:

Materials



Insulator: PBT, rated UL94V-0 (standard)
Contacts: Brass
Insulator Color: Black

Contact Plating

Underplate: 50µ" Nickel
Contact Plating: Gold Flash

Electrical

Current Rating: 1 Amp
Contact Resistance: 10 mΩ Max
Insulation Resistance: 5000 MΩ Min. @ 500 VDC
Dielectric Voltage: 1000 VAC @ 1 Minute
Operating Temp.: -55°C to 105°C



Double Row (2 x 40 Position)

TITLE		SCALE
.100" DOUBLE ROW PC HEADERS		NTS
DRAWING NO.	36-280G	
		UNITS mm
FILE NAME	36-280G.pdf	SHEET 1/1



Mode Electronics Part Number 36-280G-0