

PART#/PRODUCT SEARCH

55-212R-0

GO >>

[Item Index](#)


- Mode Catalog
- Lenline Part# Convert
- AC Adapters
- Audio Products
- Battery Holders
- Bottles and Dispensers
- Brushes
- Buzzers/Alarms
- CATV Products
- Circuit Breakers
- Coaxial Connectors
- Computer Accessories
- Connectors
- DC Power Products
- Earphones/Microphones
- Fans
- Fuseholders/Fuses
- Hardware
- IC Sockets
- Knobs
- LED Products
- Lamps/Pilot Lamps
- Miscellaneous Items
- Plastic Boxes
- Potentiometers/L-Pads
- Power Cords/Jacks/Bars
- RF Adapters
- Relays
- Rubber Feet/Grommets
- Speakers/Speaker Wire
- Switches
- Telephone Products
- Test Equipment
- Tools/Tool Cases
- Transformers
- Video Products
- Wiring Products
- Latent Fingerprint Brush**

RoHS
compliant



SUPER BRIGHT LED REPLACEMENT LAMP
T3 1/4 (10mm) Bayonet Base

These LED lamps are suitable long life replacements for T3 1/4 bayonet base lamps. With internal resistor for the specified voltage. These replacement bulbs will operate on either AC or DC voltage.



Color	Red
Volts	24V AC/DC
Brightness	21000 mcd
Forward Current	20 mA
32V Max	

- 55-212R-0** [Bulk](#)
- 55-212R-1** [Display Pkg](#)