

PART#/PRODUCT SEARCH

55-72300W-0

GO >>

[Item Index](#)

- Mode Catalog
- Lenline Part# Convert
- AC Adapters
- Audio Products
- Battery Holders
- Bottles and Dispensers
- Brushes
- Buzzers/Alarms
- CATV Products
- Circuit Breakers
- Coaxial Connectors
- Computer Accessories
- Connectors
- DC Power Products
- Earphones/Microphones
- Fans
- Fuseholders/Fuses
- Hardware
- IC Sockets
- Knobs
- LED Products
- Lamps/Pilot Lamps
- Miscellaneous Items
- Plastic Boxes
- Potentiometers/L-Pads
- Power Cords/Jacks/Bars
- RF Adapters
- Relays
- Rubber Feet/Grommets
- Speakers/Speaker Wire
- Switches
- Telephone Products
- Test Equipment
- Tools/Tool Cases
- Transformers
- Video Products
- Wiring Products
- Latent Fingerprint Brush**

RoHS
compliant



Enlarge

[How to wire LED Strips](#)
[LED Strip Specifications](#)

OUTDOOR LED STRIP 5m WHITE

- **Input Voltage:** DC 12V Regulated
- **Forward Current:** 0.4A per 1m (60 pcs LED Strip)
- **Power Dissipation:** 4.8W per 1m (60 pcs LED Strip)
- **Waterproof IP67:** 6 - Totally protected against dust, 7 - Protected against the effect of immersion between 15cm and 1m
- **Operating Temperature:** -20°C ~ 50°C

Len.[m] / LED[PCS] 5 / 300

Material Type InGaN

Emitted Color White

Lumen / meter 390

Dom. Wavelength [nm] n/a

Color Temp. [CCT] 6000

View Angle 120

55-72300W-0 Bulk

Very bright & low power consumption. Long life span LED lights, more than 50,000 hours.