
 E10480

 LR 29862



Part #	Rated Current	Breaking Capacity	Rated Voltage
55-950-0	5A	@250VAC 35A	250VAC
55-951-0	10A	@32VAC 1000A	32VAC
55-952-0	15A		
55-953-0	20A		

**Electrical Characteristic**

% of Ampere Rating	Ampere Rating	Opening Time
100%	10mA - 30A	4 hours, Minimum
135%	10mA - 30A	1 hour, Maximum
200%	10mA - 15A	5 sec., Minimum 30sec., Maximum
	20A - 30A	5 sec., Minimum 60sec., Maximum

TITLE		SCALE
<b>SLOW BLOW FUSE</b>		<b>NTS</b>
DRAWING NO. <b>55-95X</b>		
		UNITS <b>mm</b>
FILE NAME <b>55-95X.pdf</b>		SHEET <b>1/1</b>



**Mode Electronics Part Number 'multi-parts'**