


Positions	A	B	Mode Part #
2	3.96	7.92	37-702-0
4	11.88	15.84	37-704-0
6	19.80	23.76	37-706-0
8	27.72	31.68	37-708-0
10	35.64	39.60	37-710-0

Specifications:

Current Rating: 5A AC/DC
 Voltage Rating: 250V AC Max.
 Temperature Range: -25°C to 120°C
 Contact Resistance: 20 mΩ Max.
 Insulation Resistance: 1000 MΩ Min.
 Housing Material: Nylon 66, UL 94V-0 or 94V-2



A: 3.96mm * (CONTACT NO. - 1)
 B: 3.96mm * CONTACT NO.

**Includes 37-970-0 Contacts
 (Number of Contacts = Number of Positions)**

TITLE		SCALE
.156" WIRE CONNECTOR		NTS
DRAWING NO.	37-7XX	
		UNITS mm
FILE NAME	37-7XX.pdf	SHEET 1/1



Mode Electronics Part Number 'multi-parts'