

PART#/PRODUCT SEARCH

68-128-1

[GO >>](#)

[Item Index](#)

- Mode Catalog
- Lenline Part# Convert
- AC Adapters
- Audio Products
- Battery Holders
- Bottles and Dispensers
- Brushes
- Buzzers/Alarms
- CATV Products
- Circuit Breakers
- Coaxial Connectors
- Computer Accessories
- Connectors
- DC Power Products
- Earphones/Microphones
- Fans
- Fuseholders/Fuses
- Hardware
- IC Sockets
- Knobs
- LED Products
- Lamps/Pilot Lamps
- Miscellaneous Items
- Plastic Boxes
- Potentiometers/L-Pads
- Power Cords/Jacks/Bars
- RF Adapters
- Relays
- Rubber Feet/Grommets
- Speakers/Speaker Wire
- Switches
- Telephone Products
- Test Equipment
- Tools/Tool Cases
- Transformers
- Video Products
- Wiring Products
- Latent Fingerprint Brush**



AC ADAPTERS

CSA/UL wall mount adapters with 2.1mm or 2.5 mm output plug, 6' cord. Most available in centre negative or centre positive.

Voltage 12VDC @ 800mA

Type 2.1mm, center negative

68-128-1 Display Pkg

Enlarge

These AC Adapters are unregulated (except the 68-122-1, 68-519-1 and all 68-XXXXPS-1). All voltage ratings shown are at rated load. For instance a 12volt /500mA unit has an output of 12volts at 500mA. If the load is less than 500mA the output voltage will be higher. Exceeding the output current will damage the adapter. Click [here](#) to see approximate output graphs.