



**Specifications:**

- 1. Material: Copper C2680  
Thickness - 0.20mm
- 2. Plating: Nickel all over thickness at 50 $\mu$ "  
Gold Flash over Nickel - Thickness at 3 $\mu$ "
- 3. Quantity: 5,000 PCS/Reel (for 30-227-0)
- 4. General Tolerance:  $\pm 0.15$ mm
- 5. Angle Tolerance:  $\pm 1.0^\circ$
- 6. Wire: 26-28 AWG

TITLE <b>FEMALE D-SUB CRIMP CONTACTS</b>		SCALE
DRAWING NO. <b>30-228</b>		NTS
		UNITS <b>mm</b>
FILE NAME <b>30-228.pdf</b>		SHEET <b>1/1</b>



**Mode Electronics Part Number 30-228-0**