

PART#/PRODUCT SEARCH

90-152-0

GO >>

[Item Index](#)

- Mode Catalog
- Lenline Part# Convert
- AC Adapters
- Audio Products
- Battery Holders
- Bottles and Dispensers
- Brushes
- Buzzers/Alarms
- CATV Products
- Circuit Breakers
- Coaxial Connectors
- Computer Accessories
- Connectors
- DC Power Products
- Earphones/Microphones
- Fans
- Fuseholders/Fuses
- Hardware
- IC Sockets
- Knobs
- LED Products
- Lamps/Pilot Lamps
- Miscellaneous Items
- Plastic Boxes
- Potentiometers/L-Pads
- Power Cords/Jacks/Bars
- RF Adapters
- Relays
- Rubber Feet/Grommets
- Speakers/Speaker Wire
- Switches
- Telephone Products
- Test Equipment
- Tool Cases
- Tools
- Transformers
- Video Products
- Wiring Products
- Latent Fingerprint Brush**

XENON FLASH TUBE



Enlarge

Anode to Cathode voltage: 300V(200min/400 max)
Max. energy/flash rate: 4WS (watt seconds)
Flash Rate: 1/second (Min.)
Nominal Life (flashes): 10 million
Trigger Voltage: 4KV
Tube length: 32mm
Tube width: 16mm
Lead length: 40mm
Lead spacing: 10mm

90-152-0 Bulk
90-152-1 Display Pkg

