

(d)	D		H		R_1	R_2	a		b		R	M	Punch Code
M 2	3.5	0 -0.4	1.3	± 0.1	4.5	0.7	0.6	+0.15 0	0.7	± 0.1	0.1	2.2	JMP M 2.0
*(M 2.6)	4.5		1.7		6	0.9	0.8		0.9		0.1	2.6	JMP M 2.6
M 3X0.5	5.5	0 -0.5	2	± 0.15	7	1.1	0.8		1.1	± 0.15	0.1	3.5	JMP M 3.0
M 4X0.7	7		2.6		9	1.5	1		1.4		± 0.2	0.2	4.1

