



Wiring Chamber T-Block / Pin #	FUNCTION
J1 / -	V-
J1 / +	V+
J1 / GND	GROUND
J2 / 1	PORT 1 / PIN 4
J2 / 2	PORT 2 / PIN 4
J2 / 3	PORT 3 / PIN 4
J2 / 4	PORT 4 / PIN 4
J2 / 5	PORT 5 / PIN 4
J2 / 6	PORT 6 / PIN 4
J2 / 7	PORT 7 / PIN 4
J2 / 8	PORT 8 / PIN 4
J3 / 1	PORT 1 / PIN 2
J3 / 2	PORT 2 / PIN 2
J3 / 3	PORT 3 / PIN 2
J3 / 4	PORT 4 / PIN 2
J3 / 5	PORT 5 / PIN 2
J3 / 6	PORT 6 / PIN 2
J3 / 7	PORT 7 / PIN 2
J3 / 8	PORT 8 / PIN 2

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	REDRAWN IN SW	5/11/2006	


Cable Diameter
Range: 5 - 13mm




Wiring Chamber



Connections made via spring clamp terminal blocks



MATERIALS / SPECIFICATIONS	
BODY:	PBT
CABLE GLAND:	POLYAMIDE
MARKERS:	POLYAMIDE
INSERTS:	POLYAMIDE
O-RINGS:	NBR
CONTACTS:	GOLD PLATED COPPER ALLOY
RATINGS:	
AMPERAGE	3A PER PORT, 8A PER BLOCK
VOLTAGE	150V max



APPROVALS:	
US	UL LISTED
CANADA	C-UL LISTED

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MENCOM CORPORATION. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MENCOM CORPORATION IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:	
DIMENSIONS ARE IN INCHES AND [MM]	
MATERIAL	
FINISH	
DO NOT SCALE DRAWING	

NAME		MENCOM CORPORATION	
DRAWN	DWM	TITLE:	
CHECKED			
ENG APPR.			
MFG APPR.			
Q.A.			
COMMENTS:		SIZE	DWG. NO.
		B	JDC-850-019-F000
		SCALE: 1:1	WEIGHT:
		SHEET 1 OF 1	