



[SEARCH](#)

- [Home](#)
- [Company](#)
- [Products](#)
- [Resources](#)
- [Quick Buy](#)
- [Support](#)
- [Contact Us](#)
- [My Account](#)
- [My Cart](#)
- [Checkout](#)
- [Log In](#)

You're here: [Home](#) / [PG29, Shielded Gland, Nickel Brass, 0.709 - 0.984](#)



PG29, Shielded Gland, Nickel Brass, 0.709 - 0.984

Part #MCGB-29

Availability: 148 in stock.

Qty:

[ADD TO CART](#)

- [Email this Product](#)
- [Add to Product List](#)
- [Compare Product](#)

Quick Overview

Metal PG Threaded Shielded Cable Gland

Double click on above image to view full picture



Mencom Newsletter

Join our newsletter & receive the latest news from Mencom

[SIGN UP](#)



[Chat online now!](#)
Chat with us online during business hours, 8 - 5 EST

- [Specification](#)
- [Description](#)
- [Downloads](#)

Product Type	Cable Glands
Component Type	Cable Gland
Mencom Series	Shielded Gland
Shielding	Yes
Ingress Protection	IP68
Mounting Thread	PG-29
Shell / Coupling Nut Material	Nickel Brass
Male Threads	PG29
Female Threads	N/A
Gland Color	Nickel
Gland Upper Range	0.984
Gland Lower Range	0.709
Nut	Yes
Weight (lbs.)	0.2730