



You're here: [Home](#) / [ILME Rectangular Connectors](#) / [Standard, Rectangular Hood, size 77.27, 2 Pegs, Side PG29 cable entry, High Construction](#)



Standard, Rectangular Hood, size 77.27, 2 Pegs, Side PG29 cable entry, High Construction

Part # CAO-16L29

Stock: 759 in stock.

USD

Qty:

[Email this Product](#)
[Add to Product List](#)

Quick Overview

Hood for Rectangular Connector, Size 77.27

My Cart

You have no items in your shopping cart.

Mencom Newsletter

Join our newsletter & receive the latest news from Mencom



[Chat offline now](#)

Chat with us online during business hours, 8 - 5 EST

Specification	Description	Inserts	Mating Base	Mating Hood	Cable Glands	Downloads
---------------	-------------	---------	-------------	-------------	--------------	-----------

Product Type	Rectangular Connectors					
ILME Series	CN					
Mencom Series	N/A					
Component Type	Hood					
Housing/Insert Type	Standard					
Lever Type	N/A					
Pegs	2 Pegs					
Hood Entry	Side					
Hood Thread	PG29					
Enclosure Dimension	77.27					
Number of Entries	1					
Gasket/O-Ring	No					
Pin Count	N/A					
Insert Dimension	77.27					
Gender	N/A					
Contact Plating	N/A					
Double Insert	N/A					
Voltage Rating	N/A					
Amperage Rating	N/A					
Cable Length in meters	N/A					
Cable Length in feet	N/A					
Mounting Style	Cable					
Cover	No					
Upper AWG	N/A					
Lower AWG	N/A					
Termination	N/A					
Enclosure Material	Metal					
Temperature Range in Degrees Celsius	-40 C to +125 C					
IP Rating	IP66/IP67					
Weight (lbs.)	0.4160					

