



You're here: [Home](#) / [Standard, Rectangular Hood, size 77.27, 2 Pegs, Top PG29 cable entry, High Construction](#)



Standard, Rectangular Hood, size 77.27, 2 Pegs, Top PG29 cable entry, High Construction

Part # CAV-16L29

Stock: 263 in stock.

USD

Qty:

[Email this Product](#)
[Add to Product List](#)

Quick Overview

Hood for Rectangular Connector, Size 77.27

My Cart
 You have no items in your shopping cart.

Mencom Newsletter
 Join our newsletter & receive the latest news from Mencom

live chat for website
 Chat with us online during business hours, 8 - 5 EST

Specification	Description	Inserts	Mating Base	Mating Hood	Cable Glands	Downloads
---------------	-------------	---------	-------------	-------------	--------------	-----------

Product Type	Rectangular Connectors
ILME Series	CN
Mencom Series	N/A
Component Type	Hood
Housing/Insert Type	Standard
Lever Type	N/A
Pegs	2 Pegs
Hood Entry	Top
Hood Thread	PG29
Enclosure Dimension	77.27
Number of Entries	1
Gasket/O-Ring	No
Pin Count	N/A
Insert Dimension	77.27
Gender	N/A
Contact Plating	N/A
Double Insert	N/A
Voltage Rating	N/A
Amperage Rating	N/A
Mounting Style	Cable
Cover	No
Upper AWG	N/A
Lower AWG	N/A
Termination	N/A
Enclosure Material	Metal
Temperature Range in Degrees Celsius	-40 C to +125 C
IP Rating	IP66/IP67
Weight (lbs.)	0.4160

