


 You're here: [Home](#) / [MIN Size III, Cordset, 9 Pole, Male Straight, 30 Ft, 4A, Yellow, PVC](#)


MIN Size III, Cordset, 9 Pole, Male Straight, 30 Ft, 4A, Yellow, PVC

Part # MIN-9MFPX-30

Stock: 14 in stock.

 Qty:

[Email this Product](#)
[Add to Product List](#)

Quick Overview

MIN Size III (1-1/8") Male/Female Extension Cordset

My Cart

You have no items in your shopping cart.

Mencom Newsletter

Join our newsletter & receive the latest news from Mencom



Chat online now

Chat with us online during business hours, 8 - 5 EST

Specification	Description	Alternative Cordsets	Mating Receptacles	Downloads
---------------	-------------	----------------------	--------------------	-----------

Product Type	Cables
Component Type	Cordset
Mencom Series	MIN Size III
Connection Style	N/A
Pin Count	9
Gender	Male/Female Extension
Orientation Head 1	Male Straight
Mating Thread / Type Head 1	1.125-16UN2
Coupling Thread Gender1	Female
Orientation Head 2	Female Straight
Coupling Thread Gender2	Female
Upper AWG	N/A
Lower AWG	N/A
Voltage Rating	300
Amperage Rating	4
Cable Length in meters	10
Cable Length in feet	30
Cable O.D.	0.36
Cable O.D. Range	N/A
Color Code	North American
Cable Jacket Material	PVC
Jacket Color	Yellow
Armored Cordsets	N/A
Mounting Thread	N/A
Mounting Style	N/A
Nut	No
Termination	N/A
Shell / Coupling Nut Material	Clear Anodized Aluminum
Shielding	N/A
Ethernet Cable Standard	N/A
Ground Wire	Yes
Gland Upper Range	N/A
Gland Lower Range	N/A

mcvhpin	N/A
Accessories	N/A
IP Rating	IP67
Weight (lbs.)	3.1969

