


 You're here: [Home](#) / [Plastic, Rectangular Hood, size 21.21, 2 Pegs, Top PG11 cable entry, White](#)


## Plastic, Rectangular Hood, size 21.21, 2 Pegs, Top PG11 cable entry, White

Part # CK-03V

Stock: 7278 in stock.

Qty:


[Email this Product](#)  
[Add to Product List](#)

### Quick Overview

Hood for Rectangular Connector, Size 21.21

#### My Cart

You have no items in your shopping cart.

#### Mencom Newsletter

Join our newsletter &amp; receive the latest news from Mencom




#### Chat offline now

Chat with us online during business hours, 8 - 5 EST

Specification	Description	Mating Base	Inserts	Mating Hood	Cable Glands	Downloads
---------------	-------------	-------------	---------	-------------	--------------	-----------

Product Type	Rectangular Connectors					
ILME Series	CK					
Mencom Series	N/A					
Component Type	Hood					
Housing/Insert Type	Standard					
Lever Type	N/A					
Pegs	2 Pegs					
Hood Entry	Top					
Hood Thread	PG11					
Enclosure Dimension	21.21					
Number of Entries	1					
Gasket	No					
Pin Count	N/A					
Insert Dimension	21.21					
Gender	N/A					
Contact Plating	N/A					
Double Insert	N/A					
Voltage Rating	N/A					
Amperage Rating	N/A					
Mounting Style	Cable					
Cover	No					
Upper AWG	N/A					
Lower AWG	N/A					
Termination	N/A					
Enclosure Material	Plastic					
Temperature Range in Degrees Celsius	-40 C to +125 C					
IP Rating	IP44					
Weight (lbs.)	0.0380					

