


 You're here: [Home](#) / [Solenoid Valve Connectors, Field Wireable, 3 Pole, Form A 18mm, 24V, 10A, LED w/MOV, PG9 opening](#)


Solenoid Valve Connectors, Field Wireable, 3 Pole, Form A 18mm, 24V, 10A, LED w/MOV, PG9 opening

Part # VAG-029-00

Stock: 385 in stock.

Qty:

[Email this Product](#)
[Add to Product List](#)

Quick Overview

Form A (18mm) Solenoid Valve Connector

My Cart

You have no items in your shopping cart.

Mencom Newsletter

Join our newsletter & receive the latest news from Mencom


live chat for website

Chat with us online during business hours, 8 - 5 EST

Specification	Description	Mating Base	Alternative Connectors	Accessories	Cable Glands	Downloads
---------------	-------------	-------------	------------------------	-------------	--------------	-----------

Product Type	Solenoid Valve Connectors
Component Type	Field Wireable
Mencom Series	Form A 18mm
Pin Count	3
Gender	Female
Orientation Head 1	Female Right Angle
Coupling Thread Gender1	Form A 18mm
Orientation Head 2	N/A
Coupling Thread Gender2	N/A
Circuit	LED w/MOV
Upper AWG	16
Lower AWG	20
Voltage Rating	24
Amperage Rating	10
Cable Length in meters	N/A
Cable Length in feet	N/A
Cable O.D.	N/A
Cable O.D. Range	PG09 6-8mm
Color Code	DIN 43650
Cable Jacket Material	N/A
Jacket Color	N/A
Mounting Thread	PG-09
Shell / Coupling Nut Material	N/A
Gasket Type	N/A
Ground Wire	No
IP Rating	IP65
Weight (lbs.)	0.0300

