



You're here: [Home](#) / [Solenoid Valve Connectors, Field Wireable, 3 Pole, Form A 18mm, 50V, 10A, LED w/Flyback Diode, PG9 opening](#)



Solenoid Valve Connectors, Field Wireable, 3 Pole, Form A 18mm, 50V, 10A, LED w/Flyback Diode, PG9 opening

Part # VAC-029-00

Stock: 209 in stock.

Qty:

[Email this Product](#)
[Add to Product List](#)

Quick Overview

Form A (18mm) Solenoid Valve Connector

My Cart

You have no items in your shopping cart.

Mencom Newsletter

Join our newsletter & receive the latest news from Mencom

live chat for website

Chat with us online during business hours, 8 - 5 EST

Specification	Description	Mating Base	Alternative Connectors	Accessories	Cable Glands	Downloads
---------------	-------------	-------------	------------------------	-------------	--------------	-----------

Product Type	Solenoid Valve Connectors					
Component Type	Field Wireable					
Mencom Series	Form A 18mm					
Pin Count	3					
Gender	Female					
Orientation Head 1	Female Right Angle					
Coupling Thread Gender1	Form A 18mm					
Orientation Head 2	N/A					
Coupling Thread Gender2	N/A					
Circuit	LED w/Flyback Diode					
Upper AWG	16					
Lower AWG	20					
Voltage Rating	50					
Amperage Rating	10					
Cable Length in meters	N/A					
Cable Length in feet	N/A					
Cable O.D.	N/A					
Cable O.D. Range	PG09 6-8mm					
Color Code	DIN 43650					
Cable Jacket Material	N/A					
Jacket Color	N/A					
Mounting Thread	PG-09					
Shell / Coupling Nut Material	N/A					
Gasket Type	N/A					
Ground Wire	No					
IP Rating	IP65					
Weight (lbs.)	0.0300					

