







Transformer Specifications	
PRIMARY VOLTAGE(S)	230x460 (TRIPLE)
SECONDARY VOLTAGE(S)	115
RATED V.A.	1500
RATED FREQUENCY	50/60
INSULATION CLASS	130
AGENCY APPROVALS	UL,CUL
ESTIMATED WEIGHT	50.1 LBS



NOTE:
 1. FUSE CLIPS TO ACCOMMODATE 13/32-1 1/2"
 2. ALL MEASUREMENTS IN INCHES (MM)

MICRON
 ELECTRIC INDUSTRIES CORPORATION
 800 664-6600
 www.microntransformers.com

ImperVITRAN
 U.S. PAT. NO. 3,516,640
 1.5KVA 50/60HZ
 TEMP CL. 130°C

UL US LISTED 702X
 CAT. NO. B1K5BTZ13RBF
 SERIES 2 44075

SIZE	DATE	REVISION	DESCRIPTION
1	11/7/07	1	PACKAGED ACCESSORIES
2			1 PAIR OF JUMPERS

MICRON ELECTRIC INDUSTRIES CORPORATION
 17700 W. 10th Street, Suite 100
 Overland Park, KS 66204
 www.microntransformers.com

ORDER PART NO. **B1K5BTZ13RBF**