

[United States](#) > [Products & Services](#) > [Safety, Security, and Protection](#) >
[Occupational Health & Environmental Safety](#) > [Catalog](#) - [Safety Products](#)

Occupational Health & Environmental Safety

Solutions

[Pandemic & Emergency Preparedness](#)
[Welding](#)
[Hazards in the News](#)

Products & Services

[Catalog - Safety Products](#)

[Catalog - Related Products](#)
[Services](#)
[Training](#)

Resources


[Document Center](#)
[Newsletters](#)
[Regulations & Standards](#)
[Respirator Tools & Software](#)
[News](#)

Support

[Contact Us](#)
[Subscribe](#)
[Where to Buy](#)
[Sales Rep Locator](#)

[Product Catalog for OH&ES](#) > [Respiratory Protection](#) > [Maintenance - Free Particulate Respirators](#) > [3M™ Dust Respirators](#) >

3M™ Particulate Respirator 8211, N95 80/Case

 3M™ Particulate Respirator 8211, N95 80/Case

[Click to Enlarge](#)

This respirator offers all the great features of the 3M™ Particulate Respirator 8511, plus a comfortable foam face seal. Is uniquely designed to help provide protection against certain non-oil based particles. It is ideally suited for work settings that involve heat, humidity, or long periods of wear.

Where To Buy

[Where to Buy](#)
[eStore](#)

Workplace applications include grinding, sanding, sweeping, bagging and other dusty operations. It features the 3M™ Cool Flow™ Exhalation Valve, adjustable M-nose clip, comfortable foam face seal and durable braided headband to help provide a custom fit and secure seal.

3M ID: 70 - 0710 - 4255 - 3

GTIN(UPC/EAN): 5 00 51131 52750 3

Title	Content Type	File Type	Size
MSDS (United States)	MSDS	PDF	1 KB
8211 N95 Respirator, View showing face seal	Product/Single Image	JPEG	4.53 MB
8211, N95 Particulate Respirator Sales	Flyer	PDF	70 KB
8511 8211 07185 Resp User	Instructions/Manual	PDF	58 KB
Particulate Respirators 8511 and 8211, N95	Fax on Demand	PDF	111 KB

Title	Content Type	File Type	Size
-------	--------------	-----------	------

3M ID: 70 - 0710 - 4255 - 3

Minimum Order Quantity: 1 CASE

	Imperial	Metric
Length	20.900 INCH	0.531 MTR
Width	13.200 INCH	0.335 MTR
Height	11.000 INCH	0.279 MTR
Gross Weight	5.3000 LBS	2.4040 KG