

[United States](#) > [Products & Services](#) > [Safety, Security, and Protection](#) > [Occupational Health & Environmental Safety](#) > [Catalog](#) - [Related Products](#)

## Occupational Health &amp; Environmental Safety

## Solutions

[Pandemic & Emergency Preparedness](#)  
[Welding](#)  
[Wildfire Cleanup](#)  
[Hazards in the News](#)  
[Cartridge and Filter Replacement](#)

## Brands

[Speedglas™](#)

## Products &amp; Services

[Catalog - Safety Products](#)

[Catalog - Related Products](#)

## Services

[Training](#)  
[Promotions](#)

## Resources

[Product Notifications](#)  
[Respirator Tools & Software](#)  
[Media Library](#)

## News

## Support

[Contact Us](#)  
[Subscribe](#)  
[Where to Buy](#)  
[Sales Rep Locator](#)

[Product Catalog for OH&ES](#) > [Tapes and Speciality Adhesives](#) > [3M™ Electrical Tape and Related Products](#) > [Electrical Tapes](#) > [Scotch® Premium Vinyl Electrical Tape Super 88](#) >

## Scotch® Premium Vinyl Electrical Tape 88-Super2x36YD, 2 in x 36 yd (51mm x 32,9 m), 12 per case



[Click to Enlarge](#)

This black, 8.5 mil heavy duty, premium grade all -weather vinyl electrical insulating tape maintains conformability for cold weather applications. Inner pack of 1 per box, 12 per carton.

## Where To Buy

[Where to Buy](#)

## Quick Clicks

[Contact Us](#)

[Material Safety Data Sheets \(MSDS\)](#)

[OH&ES Distributor Login](#)

Scotch® Premium Vinyl Electrical Tape Super 88 offers better mechanical/abrasion resistance, and is thicker for quicker build -up. For professional use, this tape combines the flexibility of a PVC backing with excellent electrical insulating properties to provide primary electrical insulation for splices up to 600V and protective jacketing. UL Listed and CSA Certified. Excellent resistance to UV rays, abrasion, moisture, copper corrosion, alkalis and acids. Excellent all -weather performance in cold to 0°F ( -18°C) or hot to 220°F (105°C)

**3M ID:** 80 -6108 -3388 -3

**GTIN(UPC/EAN):** 0 00 54007 10356 1

### Characteristics:

Name	Value
Adhesive Material	Rubber Resin
Agency Approvals	UL Listed, CSA Certified, ASTM D 3005 type 2, Mil -I-24391C, VDE 0340 TEIL 3 -1, SS 404 09 75
Backing Material	Polyvinyl Chloride
China RoHS - Below MCV	Yes
EPC Can View	Public
EU RoHS Compliant	Yes
Operating Temperature Range	-18 to 105 Degree Celsius
Tape Color	Black
Tape Grade	Premium
Tape Type	Vinyl Electrical
Thickness	8.5 Milli -inch (Mil)