

[Shop 3M](#) > [Electrical](#) > [Terminals](#) > [Terminals](#) > [Terminals - Highland™](#) > [Disconnect - Female](#) > [Highland™ Female Disconnect Vinyl Insulated FDV14](#) > [3M™ Highland™ Female Disconnect Vinyl Insulated FDV14-250C, 16-14 AWG](#)

Search:

## Highland™ Female Disconnect Vinyl Insulated FDV14

3M Highland Female  
Disconnect Vinyl Insulated  
FDV14-250C, 16-14 AWG

### 3M™ Highland™ Female Disconnect Vinyl Insulated FDV14-250C, 16-14 AWG

This female disconnect accepts a .250 stud size.

**Stock Number:** 80610555338

**UPC:** 0-54007-70221-4

**Select Quantity:**

Case(s)/500  
Connectors  
**Price: \$97.90**

[View Larger Image](#)[Send to a Friend](#)

#### Product Details

Agency Approvals	UL and CSA
Barrel Style	Butted
China RoHS - Below MCV	No
CSA File Number	LR22190
EU RoHS Compliant	No
Fastener Orientation	Female
Insulation Material	Vinyl
Pad Width	0.250 Inch
Terminal Style	Standard
Terminal Type	Disconnect
UL File Number	E70512
Wire Gauge Range	14 to 16 American Wire Gauge (AWG)

#### Popular Products

#### Shop All Product Categories

- Abrasives
- Adhesives
- Automotive
- Bioanalytical Products
- Cleaning & Protecting
- Electrical
- Aerosols
- Electrical Fasteners
- Electrical Tapes
- Heat Shrinkable Products
- Infrared Thermometers
- Insulating & Sealing Compounds
- Lubricants & Coatings
- Personnel Grounding Products
- Terminals
- Wire Connectors
- Wire Marking & Identifying Products
- Food Service Solutions
- Fire Protection
- Home & Office
- Marine Products
- Personal Care
- Pet Care
- Professional Health Care
- Safety Products
- Tapes
- Other Products

### Shop by Promotion

- [Case Sealer Spare Parts](#)
- [Digital Projectors on Sale](#)
- [Tape Dispensers on Sale](#)

### Shop by Market

- [Car Care](#)
- [Maintenance and Repair](#)
- [Marine](#)
- [Rail](#)
- [Woodworking](#)

### Help & Support

- [Frequently Asked Questions](#)
- [Contact Shop 3M](#)
- [Terms & Conditions](#)
- [Site Map](#)



**3M:** [3M.com](#) | [Contact 3M](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2009. All Rights Reserved.