

Solutions for Electronic Specialty Markets (ESM)

Product Catalog for Electronic Specialty Markets

- 3M Electronic Specialty Markets New Product Releases
- 3M Abrasives
- 3M Adhesives, Cleaners & Compounds
- 3M Breadboards & Test Clips
- 3M Cable & Assemblies
- 3M Copper Interconnects
- 3M Fiber Optics
- 3M Fire Protection
- 3M Heat Shrink
- 3M Identification Systems
- 3M Occupational Health & Safety Products
- 3M Protective Bumpers
- 3M Reclosable Fasteners
- 3M Splicing, Terminating & Ducting
- 3M Static Control
- 3M Tapes
- 3M Terminals, Kits & Tools**
- 3M Vacuums & Accessories
- 3M Warehousing & Packaging Supplies
- 3M Wire Connectors

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors


Search This Product Catalog

By Keyword

[Product Catalog for Electronic Specialty Markets](#) [3M Terminals, Kits & Tools](#) [Electrical Wire Connectors](#) [Highland Wire Connectors](#)

## 3M Highland Wire Connector H-33, Yellow, 18-12 AWG, 100/Box

[Printer-friendly format](#)



[\[click to enlarge\]](#)

3M Highland Wire Connectors make it quick and easy to match the right connector to the size of the wire. The shells are designed to withstand temperatures up to 221°F (105°C).

3M Id : 80 - 6109 - 8125 - 2  
GTIN(UPC/EAN) : 0 00 54007 43136 7

Additional Information

3M Highland Color-Coded Wire Connectors are UL Listed, CSA Certified, and work equally well with either solid or stranded wire. H - 31, H- 33 and H - 35 connectors are rated to 600V (1000V in signs and lighting fixtures).

Learn More . . .

- [Packaging Data](#)
- [Highland Electrical Spring Connectors - Data Sheet \(PDF 12.0 K\)](#)
- [Ordering Information for Highland H - 33 Spring Connectors - Product Selection Guide \(HTML 2.3 K\)](#)

Please Note:

Adobe® Acrobat® Reader is required to view PDF documents.

Characteristics

Agency Approvals	UL and CSA
China RoHS - Below MCV	Yes
Color	Yellow
EU RoHS Compliant	Yes
Maximum Recommended Voltage Rating	600 Volt
Units per Box	100
Wire Range Capabilities	22 to 14