



Communication Technologies

- [Products](#) | [Solutions by Network](#) | [Documents & Resources](#) | [Support](#) | [Where to Buy](#) | [Contact Us](#)

[United States](#) > [All 3M Products](#) > [Electronics](#) > [Communication Technologies](#) > [Communication Technologies Product Catalog](#) > [Copper Closures and Terminals](#) > [Better Buried](#) > 3M™ Better Buried Closure Kit for Gravity Pour

3M™ Better Buried Closure Kit for Gravity Pour

3M ID 80610416242 UPC# 00054007713739 Part Number BB6X26-SB/2DC-LHS

Print Share



3M™ Better Buried Closures are rigid body splice closures designed for direct burial. When filled with 3M™ High-Gel Re-enterable Encapsulating Compound 8882, the closure can be re-entered for splice re-work.

It is suggested to use 3M™ Scotchlok™ Connectors and 3M™ MS2™/ 3M™ 710 Modules along with the Better Buried Closures. End user will need to determine if these connectors and modules are suitable for their intended application. It is required to use DR tape 68631 and B sealing tapes. These are not included in the partial kits. Kit Contents: 3M™ Better Buried Sleeves, Hose clamps, 3M™ Scotchcast™ Spacer Web 4430 (for re-entry only), 3M™ Scotchcast™ Strain Relief Bar Kits 4465 or 4465-L, 3M™ Better Buried End Caps, Funnel, Closure body, Sheath scuff material, Bonding braid, 3M™ Scotchcast™ Pair Saver 4458 or 4458W, 3M™ Scotchlok™ Shield Bond Connectors 4460-D

Need Help?

Questions? We can help
[Contact Us](#)

- Overview**
- Documents

Specifications

Applications	Buried
Approx. Compound Required Mass	12500 Gram
Approx. Compound Required Volume	13750 Milliliter
Closure Length End to End	30 Inch
Closure Size	6 x 26 Inch
Connector Type	Discrete
Cover Length	26 Inch
Encapsulant Included	No
Encapsulated	Yes
Encapsulation Method	Gravity Pour
End Cap Diameter - Multiple Entry Port #1	2.70 Inch
End Cap Diameter - Multiple Entry Port #2	2.00 Inch
End Cap Diameter - Multiple Entry Port #3	1.50 Inch
End Cap Included	(2) double port
Flame Retardant	No
Indoor/Outdoor	Outdoor
Maximum Cable Pair Count	400 Pair, 900 Pair
Maximum Discrete Pair Count	400 Pair
Maximum Modular Pair Count	900 Pair
Maximum Splice Bundle Diameter	6.00 Inch
Maximum Splice Opening - Double Sheath (Inner)	16.00 Inch
Maximum Splice Opening - Double Sheath (Outer)	19.00 Inch
Maximum Splice Opening - Single Sheath	19.00 Inch
Product Type	Closure Kit
Re-enterable	Yes
RUS Listed	Yes/BA

3M Communication Technologies: [Connect to MyTelecom](#) | [Where to Buy](#) | [Contact Us](#) | [View Mobile Site](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2015. All Rights Reserved.

