

[Home](#) Communication Technologies

- [Products](#)
- [Solutions by Network](#)
- [Documents & Resources](#)
- [Support](#)
- [Where to Buy](#)
- [Contact Us](#)

[United States](#) > [Electronics](#) > [Communication Technologies](#) > [Communication Technologies Product Catalog](#) > [Fiber Distribution Units and Enclosures](#) > [United States](#) > [Electronics](#) > [Communication Technologies](#) > [Communication Technologies Product Catalog](#) > [Fiber Distribution Units and Enclosures](#) > [3M™ Fiber Distribution Wall Mount Box, 12 Port](#)

3M™ Fiber Distribution Wall Mount Box, 12 Port

3M ID 80610934905 UPC# 00051138580568 Part Number 8432

Print Share



3M™ Wall-Mount Fiber Distribution Box 8432 offers excellent cable management in low- to medium-fiber count installations. This fiber distribution unit is secure and safe enough for mounting in high-traffic areas. The powder-coated baked epoxy and galvanized-steel construction give it added environmental and physical durability.

3M™ Wall-Mount Fiber Distribution Box 8432 comes in an attractive, low-profile design for quick and trouble-free installation anywhere in your facility. This fiber distribution unit is suitable for wall-mounted building entrances and network applications. The wall-mount box has 2 separate, lockable compartments to permit cable entry on either side top or bottom for added convenience. The unique swivel partition between the 2 chambers offers quick and convenient access to all adapters.

- Safe enough for mounting in high-traffic areas like LAN applications
- Features a separate lockable compartment for providing a demarcation point between customer and service
- Configured up to 24-port capacity and swivel partition offers easier access to adapters
- Measures 9.2 in x 15.2 in x 3.2 in
- Comes in almond color
- Grommeted cable and jumper openings reduce dust entry while ensuring physical protection
- Removable doors for ease of access during installation
- For use with discrete and ribbon riser cables
- Includes pre-assembled adapter plates to save time

Need Help?

Questions? We can help [Contact Us](#)

Overview

Documents

Specifications

| | |
|-------------------------------------|--------------------------------|
| Adapters/Coupling Pre-loaded | No |
| Color | Almond |
| Compatible Riser Cable Types | Discrete, Ribbon |
| Component Type | Fiber Distribution Unit |
| Craft Separation | Yes |
| Depth | 3.2 Inch |
| Drop Cable Connection | Termination, Direct Splice |
| Height | 9.2 Inch |
| Indoor/Outdoor | Indoor |
| Lock Compatible | Yes |
| Material | Powder Coated Galvanized Steel |
| Mount Type | Wall |
| Number of Plates | 2 |
| Number of | Max 24 |

Terminal Drops**Pigtail Pre-loaded** No**Product Series** 8432**Solution for** Access Network: FTTH/FTTB/CATV, Enterprise Network: POLS, Access Network: xDSL, Enterprise Network: Data Center, Enterprise Network: Structured Cabling**Splice Type** Mechanical, Mass Fusion, Single Fusion**Splitter Capability** No**Splitter Type** No**Stub Cable** No**Tray Capacity of Unit** 1**Width** 15.2 Inch**3M Communication Technologies:** [Connect to MyTelecom](#) | [Where to Buy](#) | [Contact Us](#) | [View Mobile Site](#)**3M:** [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.