



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
03/03/17	C	DIM. 130.80 WAS 129.03 DIM. 114.55 WAS 96.01 DIM. 55.15 WAS 59.94 DIM. 71.10 WAS 72.14 DIM. 32.15 WAS 30.23 DIM. 150.0 WAS 152.4 DIM. 3.50 WAS 3.18	T.B.	B.S.	
03/17/17	D	REDRAWN ADDED DIM. 8,12	T.B.	B.S.	




NOTES:

SPECIFICATION:

1. MATERIAL:

HOUSING : BLACK POLYPROPYLENE
 FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959
 TEMPERATURE RANGE: -10°C to +100°C
 RIVETS: BRASS, NICKLE PLTD.
 WIRE: 26 AWG, UL1007, CSA, TR64, 300V, 80°C
 SPRING: SPRING STEEL, NICKLE PLTD.
 CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER EIA-540J000
 ROHS 2 COMPLIANT

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735	Scale	Drawn By B.S.
			Approved By T.B.
decimal ±.5 (.020)	Title 4 "D" CELL HOLDER WITH WIRE LEADS		
Fractional ± .8 (.030)		Date 03/17/17	Drawing Number BH24DW
Angular ± 3°			