





SPECIFICATION:

BODY: HIGH IMPACT ABS, UL94-HB, FILE NO. E56070(S)

COLOR: BLACK

CENTER CONTACT: BRASS, NICKEL PLATED

SLIDING CONTACTS: SK5 STEEL, NICKEL PLATED

SPRING: PHOS. BRONZE WIRE WIRE STRAIN RELIEF: PVC

LED: RED, 3mm, 12V

FUSE: 250V, 3 AMP, GLASS 3AG FAST ACTING TYPE

6.35mm x 30mm (1/4" X 1 1/4") RATED AT 18 HOURS, CONTINUOUS DUTY

5 AMP'S MAX WITH CORRECT FUSE

ROHS 2 COMPLIANT

Tolerance (Inches)	Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735				
Decimal			Scale	Drawn By	B.S.
±.5 (.020)				Approved	ву Т.В.
Fractional ± .8 (.030)	Title CIGARETTE PLUG FOR 21 OR 22.2mm DIA. SOCKETS WITH RED LED, 3 AMP FUSE				
Angular ± 3°	Date 12/15/17	Drawing Number APP-001			