




Date	SYM	REVISION RECORD	AUTH	DR.	CK.
07/07/04	A	Dim. 2.05 was 2.00		B.S.	T.B.
12/02/06	B	Added "ROHS COMPLIANT"		B.S.	T.B.
5/31/13	C	UPDATED TO ROHS 2 COMPLIANT		B.S.	T.B.



Wire Leads Shown




ORDERING CODE BH4C

- L- Solder Lugs
- W- (6") Wire Leads
- SF- 9Volt type snaps
- B- Bump plates

**SPECIFICATIONS**

Plastic material - Polypropylene  
 Flammability Rating -UL94-HB, UL File NO. E216959  
 Temperature Range: -10°C to +100°C  
 Springs - Nickel Plated Spring Steel  
 Wire - 26 AWG, UL1007, CSA  
 Rivets - Brass, Nickel Plated  
 9Volt Snaps - Brass, Nickel Plated  
 CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER EIA-540J000  
 ROHS 2 COMPLIANT

Tolerance (Except as noted)	 <b>Memory Protection Devices, Inc</b> 200 Broad Hollow Road, Farmingdale, New York 11735		
	decimal ±.5 (.020)	Scale XX	Drawn By T.S. Approved By T.B.
Fractional ± .8 (.030)	Title FOUR "C" CELL HOLDER		
Angular ± 3°	Date 5/31/13	Drawing Number BH4CW	