

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151670788](#)
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 11 Circuits, 0.03m Cable Length, Tin (Sn) Plating

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-15167-001-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-15167-001-001 (PDF)	

General

Product Family	Cable
Series	15167
Comments	Contacts on opposite sides, Type D, Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	<u>Premo-Flex Cable Jumpers</u>
Product Literature Order No	987650-6631
Product Name	Premo-Flex FFC Jumper
UPC	884982925793

Physical

Cable Length	0.03m
Circuits (Loaded)	11
Circuits (maximum)	11
Material - Plating Mating	Tin
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-15167-001-001
Product Specification	PS-15167-001-001
Sales Drawing	SD-15167-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

15167 Series

Mates With

Easy-On FFC/FPC Connector:

[522071133](#) , [522711179](#) , [526101133](#) ,
[526101134](#)