

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0152660141](#)
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 14 Circuits, 0.051m Cable Length, Tin (Sn) Plating

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-15266-001-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-15266-001-001 (PDF)	

General

Product Family	Cable
Series	15266
Comments	Contacts on the same side, Type A, Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Literature Order No	987650-6631
Product Name	Premo-Flex FFC Jumper
UPC	884982430143

Physical

Cable Length	0.051m
Circuits (Loaded)	14
Circuits (maximum)	14
Net Weight	0.249/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-15266-001-001
Product Specification	PS-15266-001-001
Sales Drawing	SD-15266-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15266 Series](#)

Mates With

Easy-On FFC/FPC Connector:

[527451433](#) , [527461433](#) , [525591433](#) ,
[525591434](#)