

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0451300410](#)
Status: **Active**
Overview: Nano-Fit Power Connectors
Description: Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Dual Row, 1.0m Length, 4 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	45130
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Overmolded	No
Overview	Nano-Fit Power Connectors
Product Literature Order No	987651-6143
Product Name	Nano-Fit
Type	Discrete Wire Assembly
UPC	191128142137

Physical

Cable Length	1.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	27.837/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.46mm
Wire Size AWG	20
Wire/Cable Type	UL 1061


Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	250V AC (RMS)

Material Info

Reference - Drawing Numbers

Sales Drawing	2012341658-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[45130 Series](#)

Mates With

Nano-Fit Headers [105310](#) , [105312](#) , [105314](#)