

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0451450203**  
**Status:** **Active**  
**Overview:** Squba Sealed Wire-to-Wire Connectors  
**Description:** Squba-to-Squba Off-the-Shelf (OTS) Receptacle Cable Assembly, Single Row, 300.00mm, 2 Circuits, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">3D Model (PDF)</a>	

**General**

Product Family	Cable Assemblies
Series	45145
Application	Power, Signal, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Squba-to-Squba
Overmolded	No
Overview	<u>Squba Sealed Wire-to-Wire Connectors</u>
Product Name	Squba
Type	Discrete Wire Assembly, Sealed Assembly
UPC	191128909495

**Physical**

Cable Length	300.00mm
Circuits (Loaded)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	7.889/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.80mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	22
Wire/Cable Type	UL 1061

**Electrical**

Current - Maximum per Contact	5.0A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	451450201-000
---------------	---------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

45145 Series

**Mates With**

Squba Sealed Plug Assembly [204223](#)