

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0451460410](#)  
**Status:** **Active**  
**Overview:** [Squba Sealed Wire-to-Wire Connectors](#)  
**Description:** Squba-to-Squba Off-the-Shelf (OTS) Plug Cable Assembly, Single Row, 1.0m, 4 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">45146</a>
Application	Power, Signal, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Squba-to-Squba
Overmolded	No
Overview	<a href="#">Squba Sealed Wire-to-Wire Connectors</a>
Product Name	Squba
Type	Discrete Wire Assembly, Sealed Assembly
UPC	191128910187

**Physical**

Cable Length	1.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	26.888/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.80mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	22
Wire/Cable Type	UL 1061

**Electrical**

Current - Maximum per Contact	5.0A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	451460401-000
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[45146 Series](#)

**Mates With**

Squba Sealed Receptacle Assembly [204220](#)