

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0511140300](#)
Status: **Active**
Overview:
Description: Mighty-SPOX Wire-to-Wire Plug Housing, 3.50mm Pitch, Positive Lock, with Optional Panel Mount, 3 Circuits

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	51114
Application	Power
Overview	mightyspox
Product Name	Mighty-SPOX
UPC	800753757301

Physical

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	1677.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Product Specification	PS-51067-008
Sales Drawing	SD-51114-XX00

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[51114 Series](#)

Mates With

[51067](#)

Use With

[50419](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION