

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0747529004**
Status: **Active**
Overview: SFP+ Passive Cable Assembly
Description: SFP+-to-SFP+ Passive Cable Assembly, 10Gbps, 24 AWG Cable, Pull-to-Release Plunger Style Latch, 10.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E72548

General

Product Family Cable Assemblies
 Series 74752
 Assembly Configuration Dual Ended Connectors
 Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths., Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
 Connector to Connector SFP+-to-SFP+
 Overview SFP+ Passive Cable Assembly
 Product Name SFP Plus, SFP+
 UPC 800756711560

Physical

Cable Length 10.0m
 Circuits (Loaded) TWO DIFFERENTIAL PAIR
 Gender Male-Male
 Lock to Mating Part Yes
 Material - Metal Beryllium Copper, Zinc Alloy
 Net Weight 562.532/g
 Number of Rows 2
 Packaging Type Bag
 Single Ended No
 Waterproof / Dustproof Yes
 Wire Insulation Diameter N/A
 Wire Size AWG 24
 Wire/Cable Type Twinax

Electrical

Impedance 100Ω
 Shield Type Full Shield
 Shielded Yes
 Voltage - Maximum 3.3V

Material Info

Reference - Drawing Numbers

Sales Drawing 747520001-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

74752 Series

Mates With

74441 SFP+ Host Connector