

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0848547006**
Status: **Obsolete**
Description: DeviceNet Micro-C™ Female Plug, Thin (Drop) Cable, 1.83m (6.0') Length

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	84854
Connector to Connector	Micro-Change®-to-Pigtail
More Detailed Tech Information	DeviceNet Micro-C™ Female Plug, Thin (Drop) Cable, 1.83m (6.0ft)
Product Name	DeviceNet*, Micro-C™

Physical

Cable Length	1.83m (6.0')
Circuits (Loaded)	5
Color - Resin	Gray (1625)
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Resin	PVC
Packaging Type	N/A
Single Ended	Yes
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Size AWG	22, 24
Wire/Cable Type	PVC, Thin (Drop)

Electrical

Current - Maximum per Contact	3A, 4A
Shielded	Yes
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-84854-014, SD-84854-7001



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

84854Series