

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1800812230](#)
Status: **Active**
Overview: [Down Light Modules](#)
Description: Down Light Module 80mm, Flood - 32°, Warm White (3000K), Standard Flux

Documents:

[3D Model](#) [Product Literature \(PDF\)](#)
[Drawing \(PDF\)](#) [Installation Guide \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E328924

General

Product Family Solid State Lighting
 Series [180081](#)
 Array Type N/A
 Beam Angle 24°, 32°, and 50°
 Comments Commercially Configurable to 700mA, 1050mA, and 1400mA
 Installation Guide Order No 987650-4385
 Overview [Down Light Modules](#)
 Product Literature Order No 987650-4381
 Product Name Down Light Module
 Type LED Puck Module
 UPC 884982277762

Physical

Base Type Socket
 Color Rendering Index (CRI) 82
 Correlated Color Temp (CCT) 3000K
 Lamp Type Light Module
 Net Weight 64.640/g
 Packaging Type Individual Carton

Electrical

Lamp Wattage - Maximum 12.4W, 17.2W, 7.9W
 Lumens 490, 710, 860
 Voltage (Fixture) - Maximum 11.4V, 11.9V, 12.3V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-180081-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[180081](#) Series