

N-07-50-MH-9-C

N = CABLE TIES  
B = BASE

AMOUNT PER PACKAGE  
L = 50  
C = 100  
D = 500  
M = 1000

CABLE TIE LENGTH  
INCHES  
(ROUNDED)

COLORS  
0 = UV BLACK  
1 = BROWN  
2 = RED  
8 = GRAY  
9 = NATURAL  
30 = HEAT STABILIZED

TENSILE STRENGTH  
18 = 18 LBS  
40 = 40 LBS  
50 = 50 LBS  
120 = 120 LBS  
150 = 150 LBS  
175 = 175 LBS

TIE TYPE  
ID = IDENTIFICATION  
MH = MOUNTING HOLE  
RL = RELEASABLE  
TZ = TEFLON  
PM = PUSH MOUNT  
FL = FLAG

SALES DRAWING

EC NO: ETC2004-0223 DRWN:DMYRICK 2004/05/13 CHKD:H.BEITZL 2004/05/14 APPR:R.DEROSS 2004/05/14	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY	
		DESCRIPTION 4 PLACES 3 PLACES 2 PLACES 1 PLACE ANGULAR ±---°	mm	INCH	DIMENSION STYLE IN/MM		TITLE 19252 SERIES ENGINEERING NUMBERS CABLE TIES & BASES	
			±---	±---	DRAWN BY B.ENDERL	DATE 04/05/11	MATERIAL NO. SEE CHART	
			±---	±---	CHECKED BY H.BEITZL	DATE 04/05/11	DOCUMENT NO. SD-19252-001	
REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPROVED BY R.DEROSS	DATE 04/05/11	SHEET NO. 1 OF 1		