


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2011962300](#)  
**Status:** **Active**  
**Overview:** [Spot-On Wire-to-Board Connector System](#)  
**Description:** [Spot-On Wire-to-Board Receptacle Housing, 2.00mm Pitch, Dual Row, 30 Circuits, Natural](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification 2011960000-PS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 2011969200-200 (PDF)</a>
<a href="#">Product Specification 2011960000-A00 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 2011960000-A01 (PDF)</a>	



**General**

Product Family	Crimp Housings
Series	<a href="#">201196</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">Spot-On Wire-to-Board Connector System</a>
Product Name	Spot-On
UPC	191128047463

**Physical**

Circuits (maximum)	30
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1938.000/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2011969200-200
Product Specification	2011960000-A00, 2011960000-A01, 2011960000-PS-000
Sales Drawing	2011962300-SD-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[201196 Series](#)

**Mates With**

Spot-On Header [201197](#)

**Use With**

Receptacle Terminal [2011956000](#) , TPA Retainer [2011964150](#)