

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **2128601011**
Status: **Active**
Overview: Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Description: 2.4GHz / 5GHz Wi-Fi/Bluetooth Hinged External Antenna, with Reverse Polar SMA Male Connector, White

Documents:

| | |
|---|---|
| 3D Model | Application Specification 2128600001-AS (PDF) |
| 3D Model (PDF) | Packaging Specification 2128600001-PK1 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification 2128600001-PS (PDF) | |



General

| | |
|----------------|---|
| Product Family | Antennas |
| Series | 212860 |
| Component Type | External Antenna |
| Function | Signal |
| Mates With | Reverse Polar SMA Female Receptacle |
| Overview | Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee |
| Product Name | 2.4/5GHz Wi-Fi/BT Antenna |
| Protocol | BT, Wi-Fi |
| Type | External Antenna |
| UPC | 193264425730 |

Physical

| | |
|-------------------|-----------------|
| Length | 108.40mm |
| Mounting Style | N/A |
| Net Weight | 7.715/g |
| Packaging Type | PET Bag |
| Polarization | Linear |
| Radiation Pattern | Omnidirectional |
| Width | 9.35mm |

Electrical

| | |
|-------------------------|------------------------------|
| Band#1 F_End (MHz) | 2500 |
| Band#1 F_Start (MHz) | 2400 |
| Band#2 F_End (MHz) | 5850 |
| Band#2 F_Start (MHz) | 5150 |
| Electrical Connectivity | Cable |
| Peak Gain (dBi) | 4.5 @ 5 GHz, 5.3 @ 2.4 GHz |
| Return Loss - S11 (dB) | < -10 |
| Total Efficiency | >75% @ 5 GHz, >80% @ 2.4 GHz |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|----------------|
| Application Specification | 2128600001-AS |
| Packaging Specification | 2128600001-PK1 |
| Product Specification | 2128600001-PS |
| Sales Drawing | 2128600001-SD1 |

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

212860 Series