

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0310671010**
Status: **Active**
Overview: H-DAC 64™ Unsealed Connector System
Description: 2.54mm H-DAC 64™, 3 Way Receptacle Assembly, Single Row, Polarization A

Documents:

3D Model	Packaging Specification PK-30907-737 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-076 (PDF)
Product Specification PS-31100-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-31067-100-001 (PDF)	

General

Product Family	Crimp Housings
Series	31067
Application	Power, Wire-to-Board
Comments	Polarization Option A, Black
Overview	H-DAC 64™ Unsealed Connector System
Product Name	H-DAC 64™
UPC	800756063041

Physical

Circuits (maximum)	3
Color - Resin	Black, White
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	1.100/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +100°C

Electrical

Current - Maximum per Contact	11.0A, 9.0A
-------------------------------	-------------

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-31067-100-001
Packaging Specification	PK-30907-737, PK-31301-076
Product Specification	PS-31100-0001-001
Sales Drawing	SD-31109-003



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

[31067 Series](#)

Mates With

H-DAC 64™ 3 Way Male Housing Assembly
[31067-1040](#) , [31067-1070](#)

Use With

See Product Specification