

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010011104](#)
Status: **Active**
Overview: [KK® 508 Connector System](#)
Description: 5.08mm Pitch KK® Crimp Terminal Housing, 10 Circuits

Documents:

[3D Model](#) [Product Specification PS-99020-0087-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [3001](#)
 Application Power, Wire-to-Board
 Overview [KK® 508 Connector System](#)
 Product Name KK® 508
 UPC 800753745568

Physical

Circuits (maximum) 10
 Color - Resin Natural
 Flammability 94V-2
 Gender Receptacle
 Glow-Wire Compliant No
 Material - Resin Nylon
 Net Weight 2.831/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 5.08mm
 Temperature Range - Operating See Product Specification

Solder Process Data

Lead-freeProcess Capability WAVE

Material Info

Engineering Number 3001-10

Reference - Drawing Numbers

Product Specification PS-99020-0087-001
 Sales Drawing SDE-3001-N*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[3001](#) Series

Mates With

[3061](#) , [3003](#)

Use With

[2478](#) Crimp Terminals for 18-24 AWG, [2578](#)
 Crimp Terminals for 22-26 AWG, [2878](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION