

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008550101](#)
Status: **Active**
Overview: KK® Interconnect System - Molex
Description: KK® 254 Crimp Terminal, 22-30 AWG, Reel, Selective Gold (Au), Nickel (Ni) Under Plating

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002 \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series 2759
 Application Signal
 Crimp Quality Equipment Yes
 Overview KK® Interconnect System - Molex
 Packaging Alternative 08-55-0102 (Loose)
 Product Name KK® 254
 UPC 800753749900

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Gold
 Material - Plating Termination Nickel
 Net Weight 0.064/g
 Packaging Type Reel
 Plating min - Mating 0.381µm
 Plating min - Termination 0.762µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.57mm max.
 Wire Size AWG 22, 24, 26, 28, 30
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 2759-(555)B

Reference - Drawing Numbers

Packaging Specification PK-2759-002
 Product Specification PS-10-07-001
 Sales Drawing SD-2759



EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free
Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

2759 Series

Use With

2695 , 5051

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION